

Kwalu Features

Kwalu Classic Solid Surface

- Kwalu's proprietary outer shell is a technologically advanced, robust solid surface polymer material (1/8" thick)
- Non-coated
- Offers a warm, pleasant, wood-like temperature to the touch

Moisture Impervious

• Our Kwalu material is smooth, non-porous, and liquid impervious

Proprietary Maintenance-Free Finish

- Chemical, impact, ink, and scratch resistant
- Will not chip or crack
- 100% free of short-lived catalytic lacquers, polyurethane varnishes, delicate wood veneers, and de-laminating HPL's
- Repairable with quick strokes of steel wool
- Look of wood's enduring beauty, without undertaking its costly setbacks

Easy to Clean

- Withstands rigorous cleaning regime
- 100% bleach cleanable
- Chemically resistant, entirely smooth, high-performance solid surface (1/8" thick)
- Provide long term cleanability
- Survives All EPA's Cleaning-Disinfectant Agents
- Survives Clorox's Healthcare Portfolio of Cleaning-Disinfectant Products

24/7 10-Year Performance Warranty on Kwalu-made Frames

- Kwalu's warranty is to term, not pro-rated
- Guaranteeing both the furniture construction and Kwalu finish
- For full details of warranty offered, including any bought-out items, please refer to the Terms and Conditions of Sale https://www.kwalu.com/sales-terms-conditions/

Eco-friendly

- LEED credits available for "Material + Resources" and "Indoor Environmental Air Quality"
- Made in North America
- 99% recycled inner-steel framing and long-lasting polymers
- CARB Compliant




Product Dimensions and Specs

Overall	29W 33D 43H
Seat	23W 20.5D 19H
Arm	26H
Wt.	122 lbs
Wt. Capacity	350 lbs



Product Statement of Line Images



Acute Momentum Motorized Trendelenburg Moasdfadel: 890902 29W 33D 43H 26AH 66Ext. Depth



Product Features



Motorized Concealed Cleanout Trendelenburg Recliner

The Motorized Trendelenburg Recliner build-up behind the fully extends to a depth seat cushion. of 66 inches.

Concealed cleanout eliminates a debris



2 Button Control

Power recline is activated by pressing the 2 button control on the side of the chair.



Optional Push Bar

Add the optional push bar across the top of the chair back to aid staff in positioning the chair.



Optional Side Folding Table

An optional side folding table is available on the right side only.



Optional Side Folding Arm

To aid in easy transfer of user, an optional side folding arm is available on the left arm only. The folding feature is triggered by a latch inside the arm.

Product Foam

Foam is compliant with CAL 117 and AB 2998

Product Finishes

Frame Finish



Product Environmental Certifications

